


Drive shaft EAMB-16-7-8X15-8X10

Part number: 558034

FESTO

for adapting drives with hollow shaft



Data sheet

Feature	Value
Holder diameter 1	8 mm
Holder diameter 2	8 mm
Size	50
Nominal length	15 mm
Assembly position	Any
Max. speed	10,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	0.45 kgmm ²
Transferable torque	4.5 Nm
Product weight	20.2 g
Materials note	Conforms to RoHS