


Pressure sensor

SDE3-D10M-B-WQ4-2P-M12

Part number: 568666

FESTO



Data sheet

Feature	Value
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Materials note	Conforms to RoHS
Measured variable	1x relative pressure/1x differential pressure
Measurement method	Piezoresistive pressure sensor with display
Pressure measuring range, initial value	0 bar
Pressure measuring range, final value	10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Medium temperature	0 ... 50 °C
Ambient temperature	0 ... 50 °C
Accuracy, FS	2 %FS
Switch output	2xPNP
Switching function	Freely programmable
Switching element function	Switchable
Switching point reproducibility	0.3 %
Max. output current	100 mA
Short circuit strength	Pulsing
Operating voltage range DC	15 ... 30 V
Polarity protected	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Mounting type	with through hole with top-hat rail with wall/surface fixing
Assembly position	Any
Pneumatic connection	QS-4
Product weight	37 g
Material housing	PA-reinforced PC
Type of display	illuminated LCD
Operating status display	LCD, yellow
Setting options	Teach-In
Protection against manipulation	PIN-Code
Threshold value setting range	0 ... 100 %
Hysteresis setting range	0 ... 90 %
Protection class	IP65
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L