


Bus interface CECX-F-PB-S-V1

Part number: 565598

FESTO



Data sheet

Feature	Value
Corrosion resistance classification CRC	0 - No corrosion stress
Authorization	c UL us - Listed (OL)
Materials note	Contains PWIS substances Conforms to RoHS
Power consumption 5 V	1.4 W
Ambient temperature	5 ... 55 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	10 - 95 %
Protection class	IP20
Safety class	III
Product weight	140 g
Test for insensitivity to vibration	EN 60068-2-6 FC 5 - 9 Hz 3,5 mm 9 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Status displays	LED (status) LED red = bus fault
Fieldbus interface	PROFIBUS slave DP-V1
Fieldbus interface, connection technology	Socket Sub-D 9-pin
Fieldbus interface, transmission rate	9.6 kbit/s up to 12 mbit/s
Fieldbus interface, electrical isolation	Yes