



Parallel gripper HGPL-63-150-A

Part number: 567829
Product to be discontinued

FESTO

Type to be discontinued. Available until 2016. See Support Portal for alternative products.



Data sheet

Feature	Value
Size	63
Stroke per gripper jaw	150 mm
Max. replacement accuracy	< 0.2 mm
Max. angular gripper jaw backlash ax,ay	< 0.2 deg
Max. gripper jaw backlash Sz	< 0.05 mm
Rotationally symmetrical	<= 0.2 mm
Repetition accuracy, gripper	< 0.03 mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Gripper function	Parallel
Design structure	twin piston Guide Piston slide T-shaped Rack and pinion
Position detection	For proximity sensor
Total force at 6 bar, opening	2,466 N
Total force at 6 bar, closing	2,742 N
Working pressure	3 ... 8 bar
Max. operating frequency of gripper	< 1 Hz
Min. opening time at 6 bar	1,020 ms
Min. closing time at 6 bar	850 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	5 ... 60 °C
Gripping force per gripper jaw at 6 bar, opening	1,233 N
Gripping force per gripper jaw at 6 bar, closing	1,371 N
Mass moment of inertia	2,247.54 kgcm ²
Max. force on gripper jaw Fz static	9,000 N
Max. torque at gripper Mx static	300 Nm
Max. torque at gripper My static	200 Nm
Max. torque at gripper Mz static	250 Nm
Lubrication interval for guide components	5 Mio SP
Max. ground per external gripper finger	940 g
Product weight	18,100 g
Mounting type	Internal thread and centering sleeve With through-hole and centering sleeve
Pneumatic connection	G1/8
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information, housing	Aluminum Smooth anodized
Materials information for gripper jaws	Steel Hardened