


Mini slide DGSL-20-30-EA

Part number: 570197

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 30 mm |
| Adjustable end-position range/front length | 6.5 mm |
| Adjustable end-position range/rear length | 5.5 mm |
| Piston diameter | 25 mm |
| Drive unit operating mode | Yoke |
| Cushioning | Short elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Guide | Ball bearing cage guide |
| Structural design | Yoke Piston Piston rod Slide |
| Position sensing | For proximity sensor |
| Operating pressure | 0.1 MPa...0.8 MPa 1 bar...8 bar |
| Max. speed | 0.8 m/s |
| Repetition accuracy | 0.3 mm |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C...60 °C |
| Impact energy in the end positions | 0,45 Nm |
| Cushioning length | 1.2 mm |
| Max. force F _y | 3354 N |
| Max. force F _z | 3354 N |
| Max. torque M _x | 60 Nm |
| Max. torque M _y | 30 Nm |
| Max. torque M _z | 30 Nm |
| Theoretical force at 6 bar, retracting | 247 N |
| Theoretical force at 6 bar, advancing | 295 N |

| Feature | Value |
|-------------------------|----------------------------|
| Moving mass | 750 g |
| Product weight | 1808 g |
| Alternative connections | See product drawing |
| Type of mounting | With through-hole |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | HNBR |
| Housing material | Wrought aluminum alloy |
| Piston rod material | High-alloy stainless steel |