


Pressure sensor SPAE-P10R-S6-PNLK-2.5K

Part number: 8001446

FESTO



Data sheet

| Feature | Value |
|--|---|
| Certification | RCM compliance mark c UL us - Recognized (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Certificate issuing authority | UL E322346 |
| Note on materials | RoHS-compliant |
| Measured variable | Relative pressure |
| Method of measurement | Piezoresistive pressure sensor with display |
| Pressure measuring range initial value | 0 MPa 0 bar 0 psi |
| Pressure measuring range end value | 1 MPa 10 bar 145 psi |
| Overload pressure | 1.5 MPa 15 bar 217.5 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Temperature of medium | 0 °C...50 °C |
| Ambient temperature | 0 °C...50 °C |
| ADC resolution | 10 bit |
| Accuracy in ± % FS | 1.5 %FS |
| Repetition accuracy in ± %FS | 0.3 %FS |
| Temperature co-efficient in ± %FS/K | 0.05 %FS/K |
| Switching output | PNP/NPN switchable |
| Switching function | Freely programmable |
| Switching element function | N/C contact N/O contact Switchable |
| On time | 1 ms |
| Switch-off time | 1 ms |

| Feature | Value |
|--|--|
| Max. output current | 100 mA |
| Display range start value | 0 %FS |
| Display range end value | 99 %FS |
| Short-circuit protection | yes |
| Protocol | IO-Link® |
| IO-Link®, protocol version | Device V 1.1 |
| IO-Link®, profile | Smart sensor profile |
| IO-Link®, function classes | Binary data channel (BDC) Process data variable (PDV) Identification Diagnostics Teach channel |
| IO-Link®, communication mode | COM2 (38,4 kBd) |
| IO-Link®, SIO mode support | Yes |
| IO-Link®, port class | A |
| IO-Link®, process data width OUT | 0 Byte |
| IO-Link®, process data width IN | 2 Byte |
| IO-Link®, process data content IN | 14 bit PDV (pressure measurement) 2 bit BDC (pressure monitoring) |
| IO-Link®, minimum cycle time | 3 ms |
| IO-Link®, data memory required | 0,5 kB |
| DC operating voltage range | 18 V...30 V |
| Reverse polarity protection | for all electrical connections |
| Electrical connection | 3-wire Cable Open end |
| Cable length | 2,5 m |
| Type of mounting | Plug-in |
| Mounting position | Any |
| Pneumatic connection | Push-in sleeve QS-6 |
| Product weight | 40 g |
| Housing material | PA-reinforced |
| Sealing ring material | FPM |
| Display type | LED display 2-digit |
| Displayable unit(s) | %FS |
| Switching status indication | LED yellow |
| Setting options | IO-Link® Teach-in Via display and pushbuttons |
| Protection against tampering | PIN code |
| Setting range threshold value | 1 %...98 % |
| Degree of protection | IP40 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Class 4 according to ISO 14644-1 |