

# Electric actuator ESBF-...-32- -

Part number: 8022569

FESTO



## Data sheet

Feature	Value
Size	32
Stroke	30 mm...800 mm
Piston rod thread	M10x1.25
Screw diameter	12 mm
Max. angle of rotation of the piston rod +/-	0.25 deg
Based on norm	ISO 15552
Mounting position	Any
Motor type	Stepper motor Servo motor
Position sensing	For proximity sensor
Structural design	Electric actuator with ball screw Electric actuator with lead screw spindle
Variants	Metals with copper, zinc or nickel as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Protection against torsion/guide	With plain-bearing guide
Duty cycle	100%
Corrosion resistance class (CRC)	0 - No corrosion stress 2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 7 according to ISO 14644-1
Storage temperature	-20 °C...60 °C
For use in the food industry	See supplementary material information
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Max. radial force on actuator shaft	115 N
Max. feed force Fx	1000 N
No-load driving torque	0.1 Nm

<b>Feature</b>	<b>Value</b>
Type of mounting	With internal thread or accessory
Interface code, actuator	D32
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, smooth-anodized
Piston rod material	High-alloy stainless steel
Material of screws	Steel, galvanized
Spindle nut material	Roller bearing steel
Spindle material	Roller bearing steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized