


Air solenoid valve VUVG-B18-B52-ZT-F-1H2L-W1

Part number: 578829

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/2, bistable |
| Actuation type | Electrical |
| Valve size | 18 mm |
| Standard nominal flow rate | 1000 l/min |
| Pneumatic working port | Flange |
| Operating voltage | 24V DC |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Structural design | Piston gate valve |
| Certification | RCM compliance mark c UL us - Recognized (OL) |
| Degree of protection | IP40 With plug socket |
| Nominal width | 7.3 mm |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting Covered |
| Type of control | Pilot-controlled |
| Pilot air supply port | External |
| Lap | Overlap |
| Pilot pressure MPa | 0.15 MPa...0.8 MPa |
| Pilot pressure | 1.5 bar...8 bar |
| Changeover time | 11 ms |
| Duty cycle | 100% |
| Max. positive test pulse with 0 signal | 700 µs |
| Max. negative test pulse on 1 signal | 900 µs |
| Coil characteristics | 24 V DC: 1.0 W |
| Permissible voltage fluctuations | +/- 10 % |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |

| Feature | Value |
|--|--|
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Restricted ambient and media temperature | -5 - 50 °C Without holding power reduction |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -5 °C...60 °C |
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C...60 °C |
| Product weight | 160 g |
| Electrical connection | Via electrical sub-base |
| Type of mounting | On terminal strip |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR |
| Housing material | Wrought aluminum alloy |