


Axial kit EAMM-A-N48-90GB

Part number: 8063602

FESTO



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	17 Nm
Product weight	1378 g
Interface code, actuator	N48
Interface code, motor in	90GB
Note on materials	RoHS-compliant