


Axial kit EAMM-A-N80-90GB

Part number: 8063613

FESTO



Data sheet

| Feature | Value |
|--------------------------|----------------|
| Mounting position | Any |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C...60 °C |
| Transferable torque | 57 Nm |
| Product weight | 1755 g |
| Interface code, actuator | N80 |
| Interface code, motor in | 90GB |
| Note on materials | RoHS-compliant |