



Distributor

NEDY-L2R1-V1-Z4W2Z-U-0.3L-M8G4-5R

Part number: 8035790

FESTO



Data sheet

Feature	Value
Based on the standard	EN 61076-2-104
Authorization	RCM Mark
Design structure	Y-distributor with cables on both sides
Distributor type	2 to 1
Signal status display	Yellow LED
Additional functions	Reduction of holding current
Cable identification	With inscription label holder
Mounting type	With through-hole for M2 screw with accessories
Product weight	131 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Field device side
Electrical connection 2, design	Angular
Electrical connection 2, connection type	2x socket
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Connection pattern ZC, metric screw
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Operating voltage range DC	20.4 ... 27.6 V
Acceptable current load at 40°C	1 A
Surge strength	0.8 kV
Cable length 1	5 m
Cable length 2	0.3 m
Cable attribute	Suitable for energy chains/robot applications
Note on cable characteristics	Field device side: standard
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Torsion resistance: > 300,000 cycles, ±270°/0.1 m Energy chain: > 5 million cycles, bending radius 28 mm
Note on cable test conditions	For standard cables: Energy chain: 1.5 million cycles, bending radius 75 mm, resistance to bending: to Festo standard, test conditions on request
Minimum bending radius with freely moveable use 1	39 mm
Minimum bending radius with freely moveable use 2	30 mm
Cable diameter 1	3.8 mm
Cable diameter 2	2.9 mm
Nominal conductor cross-section	0.25 mm ²
Protection class	IP65
Ambient temperature	-10 ... 50 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole
Ambient temperature with flexible cable installation	-5 ... 50 °C

Feature	Value
Storage temperature	-10 ... 50 °C
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath color	Grey
Material housing	PA TPE-U(PUR)
Housing color	Black
Material seals	NBR TPE-O
Material electrical contact	Gold-plated copper alloy Copper alloy, tinned
Material threaded sleeve	Nickel-plated brass