

Connecting cable NEBU-M12G5-E-5-Q8N-LE5

Part number: 8078303

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 61076-2-101 IEC 61010-1
Cable designation	Without label holder
Contact durability	100
Product weight	422 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
DC operating voltage range	0 V...60 V
Operating voltage range AC	0 V...60 V
Current rating at 40° C	4 A
Surge resistance	1.5 kV
Cable length	5 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Energy chain > 5 million cycles, bending radius 75 mm
Bending radius, fixed cable installation	21 mm
Bending radius, flexible cable installation	71 mm
Cable diameter	7 mm
Cable diameter tolerance	± 0.1 mm
Cable design	5 x 1 mm ²

Feature	Value
Nominal conductor cross section	1 mm ²
Wire ends	Stripped Cut off bluntly
Degree of protection	IP65 IP68 IP69K
Note on degree of protection	In mounted state
Special features	Oil-resistant
Ambient temperature	-25 °C...80 °C
Ambient temperature with flexible cable installation	-5 °C...80 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PUR)
Housing colour	Black
Material of screw-type lock	Brass, nickel-plated
Seals material	NBR
Material of pin contacts	Copper alloy, gold-plated
Insulating sheath material	PP