



Light barrier SOOE-TB-R-PNLK-T

Part number: 8075665

FESTO



Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing department	UL E232949
Materials note	Conforms to RoHS
Measuring principle	Optoelectronic
Detection method	Through-beam sensor Transmitter Receiver
Type of light	Red LED
Max. spot diameter	65 mm at 1000 mm
Working range	0 ... 12,000 mm
Ambient temperature	-40 ... 60 °C
Switch output	Push-pull
Switching element function	Switchable PNP, dark switching NPN, light switching
Max. switching frequency	1,000 Hz
Max. output current	100 mA
Voltage drop	0 ... 1.5 V
Timer function	Via IO-Link®
Short circuit strength	Pulsing
Protocol	IO-Link
IO-Link, protocol	Device V 1.1
IO-Link, communication mode	COM2 (38,4 kBaud)
IO-Link, SIO mode support	Yes
IO-Link, port type	A
IO-Link, process data width OUT	1 bit (emitter) 2 bit (receiver)
IO-Link, process data content OUT	1 bit (emitter disable) 1 bit (hold)
IO-Link, process data width IN	2 bit (receiver)
IO-Link, process data content IN	1 bit (stability alarm) 1 bit SSC (switching signal)
IO-Link, minimum cycle time	2,3 ms
IO-Link, data memory required	2 Kilobyte
Operating voltage range DC	10 ... 30 V
Residual ripple	10 %
Idle current	14 mA
Polarity protected	for all electrical connections

Feature	Value
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw lock
Material electrical contact	Brass, gold-plated
Mounting type	With through-hole for M3 screw
Tightening torque	0.8 Nm
Assembly position	Any
Product weight	20 g
Material housing	PC PMMA
Ready status display	Green LED
Operating status display	Yellow LED
Operating reserve display	Flashing yellow LED
Setting options	IO-Link Potentiometer Teach-In
Protection class	IP65 IP67 IP69K
Insulation voltage	500 V
Surge strength	1 kV
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
Degree of contamination	3