

Mini slide DGST-16-125-E1A

Part number: 8078860

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 125 mm |
| Piston diameter | 16 mm |
| Drive unit operating mode | Yoke |
| Cushioning | Elastomer cushioning, at both ends, stroke not adjustable |
| Mounting position | Any |
| Guide | Recirculating ball bearing guide |
| Structural design | Twin piston Yoke Piston rod Slide |
| Position sensing | For proximity sensor |
| Operating pressure | 0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi |
| Max. speed | 0.5 m/s |
| Repetition accuracy | ≤ 0.3 mm |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C |
| Impact energy in the end positions | 0.15 J |
| Cushioning length | 0.8 mm |
| Max. force F _y | 960 N |
| Max. force F _z | 960 N |
| Max. torque M _x | 14 Nm |
| Max. torque M _y | 15 Nm |
| Max. torque M _z | 15 Nm |
| Theoretical force at 6 bar, retracting | 207 N |
| Theoretical force at 6 bar, advancing | 241 N |
| Moving mass | 637 g |

| Feature | Value |
|----------------------|----------------------------------|
| Product weight | 1294 g |
| Type of mounting | With through-hole |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | HNBR |
| Guide material | POM TPE-E High-alloy steel |
| Housing material | Wrought aluminum alloy |
| Piston rod material | High-alloy stainless steel |