

Compact air cylinder AEN-S-20-25-A-P-A

Part number: 8092223

FESTO



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	20 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Impact energy in the end positions	0.055 J
Theoretical force at 6 bar, retracting	26 N
Theoretical force at 6 bar, advancing	162 N
Moving mass at 0 mm stroke	18 g
Additional moving mass per 10 mm stroke	6 g
Basic weight with 0 mm stroke	65 g
Additional weight per 10 mm stroke	26 g
Type of mounting	Optionally: With through-hole With internal thread With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, anodized
Material of dynamic seals	NBR TPE-U(PU)

Feature	Value
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel