

Mini slide DGST-16-30-PA

Part number: 8085132

FESTO



Data sheet

Feature	Value
Stroke	30 mm
Adjustable end-position range/front length	22.8 mm
Adjustable end-position range/rear length	21.5 mm
Piston diameter	16 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Twin piston Yoke Piston rod Slide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. speed	0.8 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Impact energy in the end positions	0.25 J
Cushioning length	1 mm
Max. force F _y	860 N
Max. force F _z	860 N
Max. torque M _x	11.3 Nm
Max. torque M _y	7.5 Nm
Max. torque M _z	7.5 Nm
Theoretical force at 6 bar, retracting	207 N

Feature	Value
Theoretical force at 6 bar, advancing	241 N
Moving mass	318 g
Product weight	592 g
Type of mounting	With through-hole
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel