



Guide cylinder

DFM-63-80-P-A-KF-F1A

Part number: 8118956

FESTO

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths equal to or greater than 50 mm. The corresponding mounting kit, type SMB-8E, is mounted inwardly or outwardly.



Data sheet

Feature	Value
Centre of gravity distance from working load to yoke plate	50 mm
Stroke	80 mm
Piston diameter	63 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide
Position detection	For proximity sensor
Variants	Recommended for production facilities for the manufacture of lithium-ion batteries
Operating pressure MPa	0.1 ... 1 MPa
Working pressure	1 ... 10 bar
Max. speed	0.6 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 5
Ambient temperature	-5 ... 60 °C
Impact energy in end positions	1.3 Nm
Max. force F _y	1,487 N
Max. force F _y static	1,600 N
Max. force F _z	1,487 N
Max. force F _z static	1,600 N
Max. torque M _x	92.97 Nm
Max. torque M _x static	100 Nm
Max. torque M _y	47.58 Nm
Max. torque M _y static	51.2 Nm
Max. torque M _z	47.58 Nm
Max. torque M _z static	51.2 Nm
Max. permissible torque load M _x as a function of the stroke	18.67 Nm
Max. useful load as a function of the stroke at defined distance xs	233 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	1,750 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	1,870 N
Moving mass	2,731 g
Product weight	5,888 g
Centre of gravity of the moving mass as a function of the stroke	51.9 mm
alternative connections	See product drawing

Feature	Value
Pneumatic connection	G1/4
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy
Material seals	NBR
Material housing	Wrought Aluminum alloy
Material piston rod	High alloy steel, non-corrosive