

Adapter kit EHAM-MA-L9-90-L2-80

Part number: 8128229

FESTO



Data sheet

Feature	Value
Size	90
Mounting position	Any
Structural design	Standard design
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Product weight	1215 g
Type of mounting	With through-hole and screw
Interface code, base	L9-90
Interface code, layout	L2-80
Note on materials	RoHS-compliant
Adapter plate material	Aluminum, anodized
Material of screws	Steel, nickel-plated
Material of centering elements	High-alloy steel