


Parallel kit EAMM-U-38-V25-35A-63

Part number: 8093286

FESTO



Data sheet

Feature	Value
Size	38
Center-to-center distance	63 mm
Assembly position	Any
Gear unit ratio	1:1
Max. speed	3,600 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	4.35 kgmm ²
No-load driving torque	0.05 Nm
Transferable torque	0.5 Nm
Product weight	218 g
Interface code, actuator	V25
Interface code, motor in	23AB 35A
Materials note	Conforms to RoHS