


# Compact cylinder ADN-S-6-10-A-F1A

Part number: 8142514

FESTO



## Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	6 mm
Cushioning	No cushioning
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	External thread
Structural design	Piston Piston rod
Variants	Recommended for production facilities for the manufacture of lithium-ion batteries Piston rod at one end
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar 21.75 psi...116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Impact energy in the end positions	0.006 J
Theoretical force at 6 bar, retracting	9.4 N
Theoretical force at 6 bar, advancing	17 N
Moving mass	2.3 g
Product weight	11.9 g
Type of mounting	With through-hole
Pneumatic connection	M3
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy

<b>Feature</b>	<b>Value</b>
Material of dynamic seals	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy, anodized Anodized
Piston rod material	High-alloy stainless steel