

Servo motor EMMT-AS-150-L-HS-R3M

Part number: 8148325

FESTO



Data sheet

| Feature | Value |
|---|--|
| Ambient temperature | -15 °C...40 °C |
| Note on ambient temperature | Up to 80 °C with derating of -1.5% per degree Celsius |
| Max. installation height | 4000 m |
| Information on max. installation height | with 1,000 m and longer only with derating of -1.0% per 100 m |
| Storage temperature | -20 °C...70 °C |
| Relative air humidity | 0 - 90 % |
| Conforms to standard | IEC 60034 |
| Thermal class according to EN 60034-1 | F |
| Max. winding temperature | 155 °C |
| Rating class according to EN 60034-1 | S1 |
| Temperature monitoring | Digital motor temperature transmission via EnDat® 2.2 |
| Motor type as per EN 60034-7 | IM B5 IM V1 IM V3 |
| Mounting position | Any |
| Degree of protection | IP21 |
| Note on degree of protection | IP21 for motor shaft without rotary shaft seal IP65 for motor shaft with rotary shaft seal IP67 for motor housing, incl. connection technology |
| Concentricity, coaxiality, axial runout according to DIN SPEC 42955 | N |
| Balancing quality | G 2.5 |
| Detent torque | < 1.0% of peak torque |
| Bearing lifetime, under nominal conditions | 20000 h |
| Interface code, motor out | 150A |
| Electrical connection 1, connection type | Hybrid plug |
| Electrical connection 1, connection technology | M40x1 |
| Electrical connection 1, number of pins/wires | 15 |
| Contamination level | 2 |
| Note on materials | RoHS-compliant |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Vibration resistance | as per EN 60068-2-6 |

| Feature | Value |
|--|--|
| Shock resistance | as per EN 60068-2-29 15 g/11 ms as per EN 60068-2-27 |
| Certification | RCM compliance mark c UL us - Recognized (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU low voltage directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment |
| Certificate issuing authority | UL E342973 |
| Nominal operating voltage DC | 680 V |
| Type of winding switch | Star inside |
| Number of pole pairs | 5 |
| Stall torque | 45.5 Nm |
| Nominal torque | 29 Nm |
| Peak torque | 87 Nm |
| Nominal rotary speed | 2100 1/min |
| Max. rotational speed | 3495 1/min |
| Max. mechanical speed | 8000 1/min |
| Motor nominal power | 6377 W |
| Continuous stall current | 23.6 A |
| Motor nominal current | 15.4 A |
| Peak current | 49.5 A |
| Motor constants | 1.88 Nm/A |
| Standstill torque constant | 2.23 Nm/A |
| Voltage constant, phase-to-phase | 135.1 mVmin |
| Phase-phase winding resistance | 0.25 Ohm |
| Winding inductance phase-phase | 4.4 mH |
| Winding longitudinal inductivity Ld (phase) | 2.15 mH |
| Cross inductivity Lq (phase) | 2.2 mH |
| Electric time constant | 17.1 ms |
| Thermal time constant | 55 min |
| Thermal resistance | 0.39 K/W |
| Measuring flange | 450 x 450 x 30 mm, steel |
| Total output inertia moment | 57.6 kgcm ² |
| Product weight | 25400 g |
| Permissible axial shaft load | 274 N |
| Permissible radial shaft load | 1370 N |
| Rotor position sensor | Absolute encoder, multi-turn |
| Rotor position sensor for manufacturer designation | EQI 1331 |
| Rotor position encoder for absolutely detectable revolutions | 4096 |
| Rotor position sensor interface | EnDat® 22 |
| Rotor position sensor measuring principle | Inductive |
| Rotor position encoder for DC operating voltage | 5 V |
| Rotor position encoder for DC operating voltage range | 3.6 V...14 V |
| Rotor position encoder for positional values per revolution | 524288 |
| Rotor position sensor resolution | 19 bit |
| Rotor position encoder system accuracy angle measurement | -65 arcsec...65 arcsec |
| MTTF, subcomponent | 190 years, rotor position sensor |
| Energy efficiency | ENEFF (CN) / Class 1 |