



Parallel gripper DHPL-40-200-P-A

Part number: 8112226

FESTO



Data sheet

Feature	Value
Size	40
Total stroke	200 mm
Stroke per gripper jaw	100 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	≤ 0.1 deg
Max. gripper jaw backlash Sz	≤ 0.065 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.03 mm
Number of gripper fingers	2
Drive system	pneumatic
Assembly position	Any
Mode of operation	double-acting
Cushioning	P: Flexible cushioning rings/plates at both ends
Gripper function	Parallel
Gripper force back-up	No
Design structure	Rack and pinion
Guide	Plain-bearing guide
Position detection	For proximity sensor
Total gripping force at 0.6 MPa (6 bar, 87 psi), opening	1,180 N
Total gripping force at 0.6 MPa (6 bar, 87 psi), closing	992 N
Operating pressure MPa	0.15 ... 0.8 MPa
Working pressure	1.5 ... 8 bar
Operating pressure	21.75 ... 116 psi
Max. operating frequency of gripper	≤ 0.6 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	427 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	524 ms
Max. mass per external gripper finger	801 g
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP54
Ambient temperature	-10 ... 60 °C
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) opening	590 N
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) closing	496 N
Mass moment of inertia	786.9 ... 1,625 kgcm ²
Max. force on gripper jaw Fz static	750 N
Max. torque at gripper Mx static	22 Nm
Max. torque at gripper My static	22 Nm
Max. torque at gripper Mz static	22 Nm
Maintenance interval	Life-time lubrication
Product weight	6,480 g
Mounting type	Direct mounting via threads with through hole Optional

Feature	Value
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	Anodised wrought aluminium alloy
Material cover	Anodised wrought aluminium alloy
Material end plate	Anodised wrought aluminium alloy
Material housing	Anodised wrought aluminium alloy
Material gripper jaws	Anodised wrought aluminium alloy
Material piston seal	TPE-U(PU)
Material piston rod	High alloy steel, non-corrosive
Material o-ring	NBR
Material screws	Galvanized steel
Gear rack material	High alloy steel, non-corrosive
Gear material	Sintered bronze