


Vod utičnice KMEB-1-230AC-2.5

Broj artikla: 151690

FESTO

predugrađeno, za MEBH, MOEBH ventile i N2 elektromagnete.



Tehnički podaci

| Svojstvo | Vrednost |
|--|--|
| Položaj ugradnje | proizvoljno |
| Težina proizvoda | 125 g |
| Električni priključak 1 | Utičnica, to EN 175301-803, Tip C |
| Electrical connection 1, design | ugaono |
| Electrical connection 1, connection type | Utičnica |
| Electrical connection 1, cable outlet | Angled |
| Electrical connection 1, note about the cable outlet | 90° |
| Electrical connection 1, number of pins/wires | 3 |
| Electrical connection 1, type of mounting | na elektromagnetnom ventilu sa središnjim vijkom M2,5 |
| Electrical connection 2, connection technology | otvoreni kraj |
| Electrical connection 2, number of pins/wires | 3 |
| Nazivni pogonski napon AC | 230 V |
| Čvrstoća na udarno naprezanje | 4 kV |
| Priključak uzemljenja | postoji |
| Dužina kabla | 2,5 m |
| Svojstvo kabla | Standard |
| Prečnik kabla | 5,2 mm |
| Struktura kabla | 3x0,5 |
| Krajevi žica | Završetak žice |
| Mehanička zaštita | IP65 prema IEC 60529 |
| Temperatura okoline | -20 ... 80 °C |
| CE znak (vidi izjavu o usklađenosti) | prema EU-niski napon-smernica in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| Stepen zagađenja | 3 |
| Klasa korozione otpornosti KBK | 1 - Low corrosion stress |
| Material cable sheath | PVC |
| Material housing | PA66-GF30 |
| Material seals | NBR |
| Material electrical contact | Silver-plated copper alloy |