

Zaptivni prsten OL-1/8

Broj artikla: 33840

FESTO

bez propuštanja, sa metalnim telom



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	ISO 16030
Operating pressure for entire temperature range	-0,095 ... 3 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 30 bar
Operating pressure for entire temperature range	-13,775 ... 435 psi
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-40 ... 100 °C
Ručno pritezanje kod sobne temperature	Da
Nazivni moment pritezanja	6 Nm
Tolerancija uz nazivni moment pritezanja	± 20 %
Težina proizvoda	0,14 g
Pneumatski priključak	G1/8
Materijal - napomena	RoHS komformnost
Material stops	Aluminijum
Material seals	HNBR