


# Spojni vod NEBC-C-S1WA9HS-K- -N-B-LE5-PT-S10

Broj artikla: 4106124

FESTO



## Tehnički podaci

| Svojstvo   | Vrednost                             |
|--|--------------------------------------|
| Zasnovano na normi                                   | DIN 47100                            |
| Protokol   | I-Port                               |
| Cable identification                                 | Without inscription label holder     |
| Frekvencija priključivanja                           | 50                                   |
| Electrical connection 1, function                    | Field device side                    |
| Electrical connection 1, design                      | ugaono                               |
| Electrical connection 1, connection type             | Utičnica                             |
| Electrical connection 1, cable outlet                | Angled                               |
| Electrical connection 1, connection technology       | Sub-D                                |
| Electrical connection 1, number of pins/wires        | 9                                    |
| Electrical connection 1, occupied pins/wires         | 5                                    |
| Electrical connection 1, type of mounting            | 2 screws 4-40 UNC<br>With seal       |
| Electrical connection 2, function                    | Controller side                      |
| Electrical connection 2, connection type             | Kabl                                 |
| Electrical connection 2, connection technology       | otvoreni kraj                        |
| Electrical connection 2, number of pins/wires        | 5                                    |
| Područje pogonskog napona DC                         | 0 ... 30 V                           |
| Strujna opteretivost kod 40°C                        | 5,2 A                                |
| Priključak uzemljenja                                | ne postoji                           |
| Dužina kabla   | 0,5 ... 20 m                         |
| Svojstvo kabla                                       | Standard                             |
| Bending radius, fixed cable installation             | ≥ 26 mm                              |
| Bending radius, flexible cable installation          | ≥ 78 mm                              |
| Prečnik kabla  | 6,5 mm                               |
| Odstupanje prečnika kabla                            | ± 0,1 mm                             |
| Struktura kabla                                      | 5x0,5                                |
| Nazivni presek provodnika                            | 0,5 mm <sup>2</sup>                  |
| Mehanička zaštita                                    | IP65<br>IP67<br>IP69K                |
| Note on degree of protection                         | u montiranom stanju                  |
| Posebne karakteristike                               | Easy to clean                        |
| Temperatura okoline                                  | -5 ... 60 °C                         |
| Temperatura okoline kod pokretnog postepenja kablova | -5 ... 60 °C                         |
| Temperatura ležaja                                   | -20 ... 40 °C                        |
| CE znak (vidi izjavu o usklađenosti)                 | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity)         | To UK RoHS instructions              |
| PWIS conformity                                      | VDMA24364-B2-L                       |
| Materijal - napomena                                 | RoHS komformnost                     |
| Stepen zagađenja                                     | 3                                    |
| Klasa korozione otpornosti KBK                       | 3 - High corrosion stress            |
| Material cable sheath                                | PVC                                  |
| Boja izolacije                                       | sivo                                 |
| Material housing                                     | PA ojačan                            |
| Boja kućišta   | sivo                                 |
| Material screws                                      | Nerđajući čelik                      |
| Material seals                                       | EPDM                                 |
| Material electrical contact                          | Gold-plated bronze                   |
| Material insulation                                  | PVC                                  |