


# Priključni kabl KV-M12-M12-1,5

Broj artikla: 529044

FESTO

za modularni električni terminal CPX.



## Tehnički podaci

| Svojstvo   | Vrednost   |
|--|--|
| Dodatne funkcije                                     | Pin 5 of plug leading                            |
| Cable identification                                 | sa priborom                                      |
| Frekvencija priključivanja                           | 500  |
| Electrical connection 1, function                    | Field device side                                |
| Electrical connection 1, design                      | okruglo  |
| Electrical connection 1, connection type             | Utičnica   |
| Electrical connection 1, cable outlet                | Ravno  |
| Electrical connection 1, connection technology       | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires        | 5  |
| Electrical connection 1, occupied pins/wires         | 5  |
| Electrical connection 1, type of mounting            | Screw lock                                       |
| Electrical connection 2, function                    | Controller side                                  |
| Electrical connection 2, design                      | okruglo  |
| Electrical connection 2, connection type             | Utikači  |
| Electrical connection 2, cable outlet                | Ravno  |
| Electrical connection 2, connection technology       | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 2, number of pins/wires        | 5  |
| Electrical connection 2, occupied pins/wires         | 5  |
| Electrical connection 2, type of mounting            | Screw lock                                       |
| Područje pogonskog napona DC                         | 0 ... 30 V                                       |
| Područje pogonskog napona AC                         | 0 ... 30 V                                       |
| Strujna opteretivost kod 40°C                        | 4 A  |
| Čvrstoća na udarno naprezanje                        | 1,5 kV   |
| Shielding  | Da   |
| Dužina kabla   | 1,5 m  |
| Svojstvo kabla                                       | Standard   |
| Uslovi ispitivanja kabla                             | Uslovi ispitivanja na zahtev                     |
| Prečnik kabla  | 5 mm   |
| Struktura kabla                                      | 4x0,34<br>zaslonjeno                             |
| Nazivni presek provodnika                            | 0,34 mm <sup>2</sup>                             |
| Mehanička zaštita                                    | IP65<br>IP67                                     |
| Note on degree of protection                         | u montiranom stanju                              |
| Temperatura okoline                                  | -25 ... 70 °C                                    |
| Temperatura okoline kod pokretnog postepenja kablova | -5 ... 70 °C                                     |
| CE znak (vidi izjavu o usklađenosti)                 | in accordance with EU RoHS directive             |
| UKCA marking (see declaration of conformity)         | To UK RoHS instructions                          |
| PWIS conformity                                      | VDMA24364-B2-L                                   |
| Materijal - napomena                                 | RoHS komformnost                                 |
| Stepen zagađenja                                     | 3  |
| Klasa korozione otpornosti KBK                       | 2 - Moderate corrosion stress                    |
| Material cable sheath                                | TPE-U(PUR)                                       |
| Boja izolacije                                       | svetlo sivo                                      |

| Svojstvo                    | Vrednost                                 |
|-----------------------------|--|
| Material housing            | TPE-U(PUR)                               |
| Boja kućišta                | crno                                     |
| Material screw-type lock    | Nickel-plated brass                      |
| Material seals              | FPM                                      |
| Material electrical contact | Gold-plated bronze<br>Brass, gold-plated |
| Material insulation         | PVC                                      |