

# Plastično crevo

## PUN-H-10X1,5-SW-300


Broj artikla: 558253

★ Kernprogramm

dopušteno u prehrambenom području (postojano na hidrolizu).

Ovaj proizvod nije prikladan za utične priključke CN i PK.

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	10 mm
Radius savijanja, merodavan za protok	52 mm
Unutrašnji prečnik	7 mm
Min. radius savijanja	28 mm
Uputstva za korišćenje	TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1 MPa
Pogonski pritisak zavisn od temperature	-0,95 ... 10 bar
Temperature-dependent operating pressure	-13,775 ... 145 psi
Napomena za pogonski pritisak	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C
Dozvola	TÜV
Mesto izdavanja sertifikata	B 013277 0506 00
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Temperatura okoline	-35 ... 60 °C
Težina proizvoda prema dužini	0,0465 kg/m
Pneumatski priključak	For push-in connector outside diameter 10 mm
Boja	crno
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS komformnost
Material tubing	TPE-U(PU)