



Vod za programiranje VAVE-P8-VPS

Broj artikla: 570971

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	DIN 47100 EN 61076-2-101
Konstruktivna struktura	T-distributor with cable on controller side
Distributor type	1 to 2
Dodatne funkcije	Programming interface for proportional pressure regulator
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw locking with SW14
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Electrical connection 2, type of mounting	Screw locking with SW14
Electrical connection 3, function	Controller side
Electrical connection 3, design	okruglo
Electrical connection 3, connection type	Utičnica
Electrical connection 3, cable outlet	Ravno
Electrical connection 3, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 3, number of pins/wires	5
Electrical connection 3, occupied pins/wires	4
Electrical connection 3, type of mounting	Screw lock
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	2 A
Dužina kabla 1	0,15 m
Svojstvo kabla	Standard
Prečnik kabla 1	6,3 mm
Tolerance for cable diameter 1	± 0,2 mm
Struktura kabla	8x0,25 zaslonjeno
Nazivni presek provodnika	0,25 mm ²
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici

Svojstvo	Vrednost
UKCA marking (see declaration of conformity)	To UK instructions for EMC
PWIS conformity	VDMA24364-B1/B2-L
Materijal - napomena	RoHS komfornost Bez halogena
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Brass, gold-plated