

# Brtveni prsten OL-M5

Broj artikla: 34634

FESTO

bez propuštanja, s metalnim tijelom



## Tehnički podaci

| Svojstvo  | Vrijednost   |
|---|--|
| Zasnovano na normi                              | ISO 16030  |
| Operating pressure for entire temperature range | -0,095 ... 3 MPa   |
| Pogonski tlak kompletnog temperaturnog područja | -0,95 ... 30 bar   |
| Operating pressure for entire temperature range | -13,775 ... 435 psi  |
| Klasa korozione otpornosti KBK                  | 2 - umjerena otpornost na koroziju   |
| PWIS conformity                                 | VDMA24364-B2-L   |
| RSBP classification to CD-0033                  | F1a  |
| Klasa čistog prostora                           | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Temperatura okoline                             | -40 ... 100 °C   |
| Ručno pritezanje kod sobne temperature          | da   |
| Nazivni moment pritezanja                       | 2,5 Nm   |
| Tolerancija uz nazivni moment pritezanja        | ± 20 %   |
| Težina proizvoda                                | 0,06 g   |
| Pneumatski priključak                           | M5   |
| Materijal - napomena                            | RoHS sukladno  |
| Material stops                                  | Aluminij   |
| Material seals                                  | HNBR   |