


Bus node CTEU-AS

Broj artikla: 572555

FESTO



Tehnički podaci

Svojstvo	Vrednost
Protokol	AS-Interface
Dimenzije Š x D x V	40 mm x 91 mm x 50 mm
Mera mreže	40 mm
Vrsta pričvršćenja	On electrical interface On electrical connection block
Težina proizvoda	90 g
Temperatura okoline	-5 ... 50 °C
Temperatura ležaja	-20 ... 70 °C
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju Unused connections sealed
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Dozvola	c UL us - Listed (OL)
Materijal - napomena	RoHS komfornost
Material housing	PA
LED-prikaz specifičan za proizvod	PS: radni napon za napajanje elektronike i opterećenja X1: Stanje sistema modul I-ulaz 1
LED-prikaz specifičan za sabirnicu	AS-i: AS-interface - pogon
Dijagnoza	Communication error System diagnostics Podnapon
Kontrolni elementi	DIL prekidač
Fieldbus interface	AS-Interface
Fieldbus interface, protocol	AS-Interface
Fieldbus interface, type of connection	Utikači
Fieldbus interface, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Fieldbus interface, number of pins/wires	4
Fieldbus interface 2, function	Bus connection outgoing Power supply
Fieldbus interface 2, connection type	Utičnica
Fieldbus interface 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Fieldbus interface 2, number of pins/wires	4
Maksimalna zapremina adrese za ulaze	2 Byte
Maksimalna zapremina adrese za izlaze	2 Byte
Konfiguracija parametara	Watchdog disable Watchdog enable
Interno vreme ciklusa	10 ms
Podrška konfiguracije	bez
Područje pogonskog napona DC	20 ... 31,6 V
Nazivni pogonski napon DC	30 V
Maks. Napajanje	4 A
Sopstvena potrošnja struje kod pogonskog napona	Tip. 50 mA