



Spojni vod NEBS-L1G4-K-2.5-LE4

Broj artikla: 572576

★ Kernprogramm

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	With inscription label holder
Frekvencija priključivanja	100
Težina proizvoda	53 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Connection pattern L1J
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Snap-in locking
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 30 V
Strujna opteretivost kod 40°C	1 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabla	2,5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 13 mm
Bending radius, flexible cable installation	≥ 42 mm
Prečnik kabla	4,1 mm
Odstupanje prečnika kabla	± 0,2 mm
Struktura kabla	4x0,17
Nazivni presek provodnika	0,17 mm ²
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP40
Note on degree of protection	u montiranom stanju
Temperatura okoline	-20 ... 60 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 60 °C
Temperatura ležaja	-20 ... 60 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Materijal - napomena	RoHS komfornost
Stepen zagađenja	2
Klasa korozione otpornosti KBK	4 - Very high corrosion stress
Material cable sheath	PVC
Boja izolacije	sivo
Material housing	PA
Boja kućišta	belo
Material electrical contact	Tin-plated bronze
Material insulation	PVC