


# Razdelnik NEDY-

Broj artikla: 8032867

FESTO



## Tehnički podaci

Ukupni list podataka - Pojedinačne vrednosti zavise od Vaše konfiguracije.

Svojstvo	Vrednost
Dozvola	RCM Mark
Distributor type	2 to 1
Indikacija pogonske spremnosti	LED zeleni
Indikacija stanja	LED žuti
Signal status display	LED žuti
Dodatne funkcije	Smanjenje struje držanja
Cable identification	With inscription label holder Without inscription label holder
Vrsta pričvršćenja	With through-hole for M2 screw sa priborom
Electrical connection 1, function	Controller side
Electrical connection 1, connection type	Kabl Utikači
Electrical connection 1, cable outlet	Ravno Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101 M8x1, A-coded to EN 61076-2-104 otvoreni kraj
Electrical connection 1, number of pins/wires	3 4
Electrical connection 2, function	Field device side
Electrical connection 2, connection type	2 x utičnica 2x cable
Electrical connection 2, cable outlet	Ravno Angled Rotatable
Electrical connection 2, connection technology	Connection pattern ZB, self-tapping screw Connection pattern ZC, self-tapping screw Connection pattern ZC, metric screw Connection pattern H Plug pattern type A to EN 175301-803 Plug pattern type B to EN 175301-803 Plug pattern type B to industry standard, 11 mm Plug pattern type C to EN 175301-803 Connection pattern type C to industry standard, 9.4 mm M12x1, A-coded in accordance with EN 61076-2-101 M8x1, A-coded to EN 61076-2-104 otvoreni kraj
Electrical connection 2, number of pins/wires	2 3 4 5
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V

Svojstvo	Vrednost
Strujna opteretivost kod 40°C	0,5 ... 4 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabla 1	0,3 ... 30 m
Dužina kabla 2	0,3 ... 30 m
Svojstvo kabla	Suitable for energy chains/robot applications
Nazivni presek provodnika	0,14 mm <sup>2</sup> 0,25 mm <sup>2</sup>
Temperatura okoline	-25 ... 85 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost Bez halogena Free of phosphoric acid ester
Stepen zagađenja	3
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	PA PC TPE-U(PUR)
Boja kućišta	crno