

Brtni prsten

OL-1/4-200

Broj artikla: 534233

FESTO

bez propuštanja, s metalnim tijelom



Tehnički podaci

Svojstvo	Vrijednost
Zasnovano na normi	ISO 16030
Veličina pakiranja	200
Operating pressure for entire temperature range	-0,095 ... 3 MPa
Pogonski tlak kompletnog temperaturnog područja	-0,95 ... 30 bar
Operating pressure for entire temperature range	-13,775 ... 435 psi
Klasa korozione otpornosti KBK	2 - umjerena otpornost na koroziju
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
Klasa čistog prostora	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-40 ... 100 °C
Ručno pritezanje kod sobne temperature	da
Nazivni moment pritezanja	10 Nm
Tolerancija uz nazivni moment pritezanja	± 20 %
Pneumatski priključak	G1/4
Materijal - napomena	RoHS sukladno
Material stops	Aluminij
Material seals	HNBR