


# Krajnja ploča CPX-AP-A-EPR

Broj artikla: 8112477

FESTO



## Tehnički podaci

Svojstvo	Vrijednost
Dimenzije Š x D x V	(installation dimensions) 30,4 mm x 117,2 mm x 53,6 mm
Mjera rastera	50,1 mm
Vrsta pričvršćenja	Izravna ugradnja pomoću prolaznih rupa Na H-šini s priborom Via through-hole for M5 screw Via through-hole for M6 screw
Težina proizvoda	116 g
Položaj ugradnje	Any, on H-rail: horizontal
Temperatura okoline	-20 ... 50 °C
Informacija o temperaturi okoline	Note ambient temperature derating according to IEC 61131-2:2017
Temperatura ležaja	-20 ... 70 °C
Relativna vlažnost zraka	5 - 95 % ne kondenzira se
Nominal altitude of use	≤ 2000 m ASL (≥ 79,5 kPa)
Max. installation height	3.500 m
Note on max. installation height	> 2000 m ASL (≤ 79,5 kPa) Note ambient temperature derating according to IEC 61131-2:2017
Klasa korozione otpornosti KBK	1 - niska otpornost na koroziju
Otpornost na vibracije	Ispitivanje transporta sa stupnjem oštine 2 prema FN 942017-4 i EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Ispitivanje transporta sa stupnjem oštine 1 prema FN 942017-4 i EN 60068-2-6
Udarna čvrstoća	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms to EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27
Klasa zaštite	III
Overvoltage category	II
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS sukladno Bez halogena Bez estera fosforne kiseline
Material end plate	Die-cast aluminium, coated
Material screws	Steel, nickel-plated
Material seals	PU-pjena