

Plastično crevo PFAN-3X0,5-NT

Broj artikla: 8061167

FESTO



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	3 mm
Radius savijanja, merodavan za protok	30 mm
Unutrašnji prečnik	2,3 mm
Min. radius savijanja	10 mm
Uputstva za korišćenje	Tubing without printing
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1,5 MPa
Pogonski pritisak zavisn od temperature	-0,95 ... 15 bar
Temperature-dependent operating pressure	-13,775 ... 217,5 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information See declaration of conformity
Note on temperature of medium	Water vapour: max. 120°C
Temperatura okoline	-20 ... 150 °C
Težina proizvoda prema dužini	0,0075 kg/m
Pneumatski priključak	For push-in connector outside diameter 3 mm for barbed connector internal diameter 2 mm with nut
Boja	prirodno
Tvrdoća po Shoreu	D 60 +5
Materijal - napomena	RoHS komformnost
Material tubing	PFA