


Pajungimo kabelis

NEBS-SM12G12-E-0.5-N-LE12

Gaminio numeris: 3947401

FESTO



Tech. Duomenys

Savybės	Reikšmė
Atitinka standartus	EN 61076-2-101
Cable identification	su priedais
Prijungimo dažnis	100
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištukas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw locking with hex SW13
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	12
Electrical connection 2, occupied pins/wires	12
Nominalus DC įtampos lygis	0 ... 30 V
Nominalus AC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	1,5 A
Atsparumas smūgiams	0,5 kV
Kabelio ilgis	0,5 m
Kabelio priedas	Suitable for energy chains
Laido bandymo sąlygos	Bandyamas pagal užklausimą
Bending radius, fixed cable installation	≥ 32 mm
Bending radius, flexible cable installation	≥ 65 mm
Kabelio skersmuo	6,5 mm
Kabelio struktūra	12x0,25
Nominalus laidininko skerspjuvis	0,25 mm ²
Laido galai	Cut off bluntly
Apsaugos klasė	IP67
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-5 ... 70 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 70 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	Juodas
Material housing	TPE-U(PUR)
Korpuso spalva	Juodas
Material screw-type lock	Nickel-plated die-cast zinc
Material electrical contact	Brass, gold-plated