

Spojni vod NEBL-T12W4-E-2-N-LE4

Broj artikla: 8080778

FESTO



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61076-2-111
Dozvola	c UL us - Listed (OL)
Mesto izdavanja sertifikata	UL E504946
Cable identification	Without inscription label holder
Težina proizvoda	243 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, T-coded to EN 61076-2-111
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 63 V
Strujna opteretivost kod 40°C	12 A
Čvrstoća na udarno naprezanje	1,5 kV
Shielding	ne
Dužina kabla	2 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 42 mm
Bending radius, flexible cable installation	≥ 84 mm
Prečnik kabla	8,4 mm
Odstupanje prečnika kabla	± 0,25 mm
Struktura kabla	4x1,5
Nazivni presek provodnika	1,5 mm ²
Krajevi žica	Sheath removed
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	crno
Material housing	PA

Svojstvo	Vrednost
Boja kućišta	crno
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Mesing
Material insulation	PP