

Unitate ghidare FENG-50- -KF

Numar piesa: 34489

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	50
Cursa	10 mm...500 mm
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Forta max. Fy	1260 N
Forta max. Fy statica	1600 N
Forta max. Fz	1260 N
Forta max. Fz statica	1600 N
Moment max. Mx	65 Nm
Moment max. Mx static	83 Nm
Max. Moment My	70 Nm
Moment My static max.	89 Nm
Moment max. Mz	70 Nm
Moment Mz static max.	89 Nm
Forta de deplasare	15 N
Supraincarcare masa mobila pentru fiecare cursa de 10 mm	49 g
Greutate de baza la o cursa de 0 mm	4030 g
Greutate suplimentara pe cursa de 10 mm	49 g
Centrul de greutate al masei in miscare la o cursa de 0 mm	60 mm
Centrul de greutate suplimentar al masei in miscare la o cursa de 10 mm	4.7 mm
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	Otel calit
Material carcasa	Aliaj de aluminiu forjat, anodizat
Material placa de jug	Aliaj de aluminiu forjat, anodizat