


# Krajnja ploča VMPAL-EPL-AP

Broj artikla: 8087171

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Položaj priključka	gore
Zaštita od zamene polova	Da
Diagnostics via LED	Diagnostics per module Power supply load
Diagnostics per internal communication	Electronics/sensors overvoltage Electronics/sensors undervoltage
Maks. broj ventilskih mesta	32
Struktura ventilskog bloka	Valve sizes can be mixed
Maksimalni broj elektromagnetnih kalema	32
Dimenzije Š x D x V	43,1 mm x 107,5 mm x 50,2 mm
Osiguranje (kratki spoji)	interni elektronski osigurač po kanalu
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 30 mA
Intrinsic current consumption at nominal operating voltage load	Tip. 15 mA
Max. power supply	2 x 4 A (external fuse required)
Nominal operating voltage DC for electronics/sensors	24 V
Nominal operating voltage, DC outputs	24 V
Premošćenje kvara mreže	10 ms
Electrical isolation of outputs between channel - internal communication	Da
Permissible voltage fluctuations for electronics/sensors	± 25 %
Permissible voltage fluctuations, load	± 10 %
Power supply, function	Incoming electronics/sensors and load
Power supply, type of connection	Utikači
Power supply, connection technology	M8x1, A-coded to EN 61076-2-104
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	Utičnica
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Dozvola	RCM Mark
KC mark	KC-EMV
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Klasa korozione otpornosti KBK	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Temperatura ležaja	-40 ... 70 °C
Relativna vlažnost vazduha	5 - 95 % ne kondenzira se
Zaštita od direktnog i indirektnog dodira	Protective extra-low voltage with safe disconnection (PELV) Protection by safety extra-low voltage (SELV)
Mehanička zaštita	IP65 IP67
Note on degree of protection	u montiranom stanju Unused connections sealed

Svojstvo	Vrednost
Temperatura okoline	-5 ... 50 °C
Nominal altitude of use	≤ 2000 m NHN
Maks. pritezni moment	1,7 Nm
Težina proizvoda	194 g
Maks. dužina voda	50 m system communication
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2 x utičnica
Communication interface, connection technology	M8x1, D-coded to EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP-COM
Communication interface, screening	Da
Vrsta pričvršćenja	Vučno sidro
Materijal - napomena	RoHS komfornost
Material housing	Die-cast aluminium, painted PA ojačan
Material threaded sleeve	Mesing niklovan