


IO-Link Master USB CDSU-1

Broj artikla: 8091509

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61131-9
Uputstva za korišćenje	For use with the USB IO-LinkMaster Tool software (available from the Support Portal) for Windows version 7 or higher (32/64 bit).
Input voltage	5 V DC at the USB connection 24 V DC \pm 6 V via external supply
Input current	Max. 2.5 A via external supply Max. 600 mA at the USB connection
Output voltage	24 V DC \pm 10% with USB operation 24 V DC \pm 6 V with external supply (max. input voltage)
Zaštita od zamene polova	za priključke pogonskog napona
Otpornost na kratak spoj	Da
Otpornost na preopterećenje	ne postoji
Dozvola	RCM Mark
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Temperatura ležaja	-10 ... 75 °C
Mehanička zaštita	IP20
Temperatura okoline	0 ... 55 °C
Težina proizvoda	106 g
Protokol	IO-Link
IO spoj, protokol	Master V 1.0 Master V 1.1
IO spoj, modus komunikacije	COM1 (4,8 kBaud), COM2 (38,4 kBaud), COM3 (230,4 kBaud)
IO spoj, tip porta	A B, with accessories
IO spoj, broj portova	1
IO spoj, širina procesnih podataka OUT	can be parameterised 0 - 32 bytes
IO spoj, širina procesnih podataka IN	can be parameterised 0 - 32 bytes
IO spoj, minimalno vreme ciklusa	1,5 ms
IO spoj, memorija	2 kByte / Port
IO spoj master, izlazna struja	80 mA with USB operation Max. input current with external supply
Power supply, function	Additional power supply
Power supply, type of connection	Utičnica
Power supply, connection technology	Coaxial
Power supply, note on connection technology	for plugs with outside diameter 5.5 mm/inside diameter 2.1 mm
Power supply, number of pins/wires	2
USB interface, connection technology	USB 2.0 type B mini
USB interface, connection pattern	00995868
USB interface, galvanic isolation	Da
Electrical connection for IO-Link®, connection type	Utičnica
Electrical connection for IO-Link®, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for IO-Link®, number of pins/wires	5
IO-Link® electrical connection, occupied pins/wires	3
Materijal - napomena	RoHS komformnost
Material housing	Anodised wrought aluminium alloy