



Vod enkodera

NEBM-REG6-E-20-Q14N-REG6

Broj artikla: 8097201

★ Kernprogramm

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Connection pattern RE
Electrical connection 1, number of pins/wires	6
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	Connection pattern RE
Electrical connection 2, number of pins/wires	6
Electrical connection 2, occupied pins/wires	6
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	1,6 A
Čvrstoća na udarno naprezanje	2 kV
Dužina kabela	20 m
Svojstvo kabela	Suitable for energy chains
Uslovi ispitivanja kabela	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 55 mm
Bending radius, flexible cable installation	≥ 55 mm
Prečnik kabela	7,4 mm
Struktura kabela	2x0,51+4x0,205
Nazivni presek provodnika	0,205 mm ² 0,51 mm ²
Nominal conductor cross section (AWG)	AWG20 AWG24
Mehanička zaštita	IP20
Note on degree of protection	u montiranom stanju
Temperatura okoline	-40 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-10 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	PVC
Boja izolacije	crno
Material housing	PVC
Boja kućišta	sivo
Material insulation	PVC