


Reductor EMGA-80-A-G12-100A

Cod: 8141748

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	80 mm
Motor cu flansa	100 mm
Joc de rasucire	0,25 deg
tipul reductorului	Reductor in unghi drept
Raport de transmisie	12:1
Viteza maxima de intrare	7.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	120 Nm
Momentul de inertie al angrenajului	1,379 kgcm ²
Cuplu maxim iesire	240 Nm
Eficienta maxima	94 %
rigiditate la torsiune	5 Nm/arcmin
Greutate produs	5.100 g
Interfata reductor arbore de iesire	80G
Interfata reductor arbore de antrenare	100A
Indicatie material	conform RoHS