


# Utično podnožje NEFV-V14-XX4G3-T1G3

Broj artikla: 8109878

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Dimenzije Š x D x V	18,7 mm x 50 mm x 15,3 mm
Vrsta pričvršćenja	With through-hole for M3 screw
Cable outlet	Ravno
Težina proizvoda	6,8 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, connection technology	ZIF
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	Plug-in
Electrical connection 2, function	Field device side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utičnica
Electrical connection 2, connection technology	ZIF
Electrical connection 2, number of pins/wires	12
Electrical connection 2, occupied pins/wires	3
Electrical connection 2, type of mounting	Plug-in
Electrical connection 3, function	Controller side
Electrical connection 3, design	ugaono
Electrical connection 3, connection type	Utikači
Electrical connection 3, connection technology	Festo-specific coding
Electrical connection 3, number of pins/wires	3
Electrical connection 3, occupied pins/wires	3
Electrical connection 3, type of mounting	Plug-in
Područje pogonskog napona DC	0 ... 310 V
Priključak uzemljenja	ne postoji
Shielding	ne
Mehanička zaštita	IP40
Note on degree of protection	u montiranom stanju
Temperatura okoline	-10 ... 60 °C
Temperatura ležaja	-40 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	2
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material housing	PA
Boja kućišta	crno
Material electrical contact	Nickel-plated and gold-plated bronze