

Spojni vod NEBC-D8W4-ES-50-N-S-D8W4-ET

Broj artikla: 8146040

FESTO



Tehnički podaci

| Svojstvo | Vrednost |
|--|---|
| Zasnovano na normi | EN 61076-2-114 |
| Dozvola | c UL us (OL) |
| Mesto izdavanja sertifikata | UL E520706 |
| Cable identification | Without inscription label holder |
| Frekvencija priključivanja | 100 |
| Težina proizvoda | 2.917 g |
| Electrical connection 1, function | Controller side |
| Electrical connection 1, design | okruglo |
| Electrical connection 1, connection type | Utikači |
| Electrical connection 1, cable outlet | Angled |
| Electrical connection 1, connection technology | M8x1, D-coded to EN 61076-2-114 |
| Electrical connection 1, number of pins/wires | 4 |
| Electrical connection 1, occupied pins/wires | 4 |
| Electrical connection 1, type of mounting | Screw-type lock with longitudinal knurl |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, design | okruglo |
| Electrical connection 2, connection type | Utikači |
| Electrical connection 2, cable outlet | Angled |
| Electrical connection 2, connection technology | M8x1, D-coded to EN 61076-2-114 |
| Electrical connection 2, number of pins/wires | 4 |
| Electrical connection 2, occupied pins/wires | 4 |
| Electrical connection 2, type of mounting | Screw-type lock with longitudinal knurl |
| Područje pogonskog napona DC | 0 ... 30 V |
| Nazivni pogonski napon DC | 24 V |
| Strujna opteretivost kod 40°C | 3 A |
| Čvrstoća na udarno naprezanje | 1,5 kV |
| Zaštita od zamene polova | ne |
| Priključak uzemljenja | ne postoji |
| Shielding | Da |
| Svojstva prenošenja | as per system communication AP |
| Dužina kabla | 50 m |
| Svojstvo kabla | Suitable for energy chains |
| Uslovi ispitivanja kabla | Uslovi ispitivanja na zahtev |
| Bending radius, fixed cable installation | ≥ 20 mm |
| Bending radius, flexible cable installation | ≥ 75 mm |
| Prečnik kabla | 6,3 mm |
| Odstupanje prečnika kabla | ± 0,2 mm |
| Struktura kabla | 1x(4xAWG22) |
| Nominal conductor cross section (AWG) | AWG22 |
| Mehanička zaštita | IP65 IP67 |
| Note on degree of protection | u montiranom stanju |
| Posebne karakteristike | postojano na ulje |
| Temperatura okoline | -20 ... 60 °C |
| Temperatura okoline kod pokretnog postepenja kablova | -5 ... 60 °C |
| Temperatura ležaja | -40 ... 70 °C |

| Svojstvo | Vrednost |
|--|--------------------------------------|
| CE znak (vidi izjavu o uskladenosti) | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| Materijal - napomena | RoHS komformnost Bez halogena |
| Stepen zagađenja | 3 |
| Klasa korozione otpornosti KBK | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| Boja izolacije | Silver-grey with sky blue stripe |
| Material housing | PA TPE-U(PUR) |
| Boja kućišta | crno |
| Material screw-type lock | Nickel-plated brass |
| Material seals | NBR |
| Material electrical contact | Gold-plated copper alloy |
| Material insulation | PP |