



Prigušno-nepovratni ventil VFOE-LS-T-R18-Q8-F1A

Broj artikla: 8157626

FESTO



Tehnički podaci

Svojstvo	Vrednost
Funkcija ventila	Prigušno-nepovratna funkcija dolaznog vazduha
Pneumatski priključak 1	QS-8
Pneumatski priključak 2	R1/8
Način aktiviranja	ručno
Element podešavanja	Okretno dugme sa blokadom
Vrsta pričvršćenja	navojno
Normalni nazivni protok u smeru prigušivanja	170 l/min
Normalni nazivni protok u povratnom smeru	130 ... 200 l/min
Temperatura okoline	-10 ... 60 °C
Material housing	PBT
Položaj ugradnje	proizvoljno
Otvor ključa	13 mm
Zakretljivost	360°/nije dozvoljena trajno okretanje
Varijante	Recommended for production facilities for the manufacture of lithium-ion batteries
Operating pressure for entire temperature range	0,02 ... 1 MPa
Pogonski pritisak kompletnog temperaturnog područja	0,2 ... 10 bar
Operating pressure for entire temperature range	2,9 ... 145 psi
Standard flow rate in flow control direction 0.6->0 MPa (6->0 bar, 87->0 psi)	270 l/min
Standard flow rate in non-return direction at 0.6->0 MPa (6->0 bar, 87->0 psi)	320 ... 390 l/min
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:4:4]
Napomena o mediju pogona i upravljanja	Nauljeni pogon je moguć (u daljnjem pogonu potreban)
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 4
Temperatura medijuma	-10 ... 60 °C
Težina proizvoda	9,5 g
Materijal - napomena	RoHS komfornost
Material cover	PBT
Material of dynamic seals	HNBR
Material threaded bolt	Steel, chemical nickel-plated
Material release ring	PBT
Material static seals	NBR