



Motorski vod

NEBM-H6G4-E-10-Q13N-LE4

Broj artikla: 5219200

★ Kernprogramm

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Connection pattern H6, coded for the motor
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 300 V
Područje pogonskog napona AC	0 ... 300 V
Strujna opteretivost kod 40°C	9,5 A
Čvrstoća na udarno naprezanje	2 kV
Dužina kabla	10 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 55 mm
Bending radius, flexible cable installation	≥ 55 mm
Prečnik kabla	7,3 mm
Struktura kabla	4x0,79
Nazivni presek provodnika	0,79 mm ²
Nominal conductor cross section (AWG)	AWG18
Krajevi žica	Završetak žice
Mehanička zaštita	IP20
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 90 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 90 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	PVC
Boja izolacije	crno
Material housing	PA
Boja kućišta	belo
Material insulation	PVC