


Priključni kabl NEBV-M12G8-KD-3-M12G4

Broj artikla: 547888

FESTO

za proporcionalni regulator pritiska VPPM.



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	DIN 47100 EN 61076-2-101
Konstruktivna struktura	Y-distributor with cables on both sides
Distributor type	1 to 2
Dodatne funkcije	Distribution of the analogue inputs and outputs of a proportional pressure regulator
Cable identification	Without inscription label holder
Vrsta pričvršćenja	With through-hole for M3 screw
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utičkači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw lock
Electrical connection 3, function	Controller side
Electrical connection 3, design	okruglo
Electrical connection 3, connection type	Utičkači
Electrical connection 3, cable outlet	Ravno
Electrical connection 3, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 3, number of pins/wires	4
Electrical connection 3, occupied pins/wires	3
Electrical connection 3, type of mounting	Screw lock
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	2 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabla 1	2,5 m
Dužina kabla 2	0,5 m
Svojstvo kabla	Standard
Bending radius 1, fixed cable installation	≥ 33 mm
Minimum bending radius with freely moveable use 1	≥ 66 mm
Bending radius 2, fixed cable installation	≥ 33 mm
Minimum bending radius with freely moveable use 2	≥ 66 mm
Prečnik kabela 1	6,3 mm

Svojstvo	Vrednost
Tolerance for cable diameter 1	± 0,2 mm
Prečnik kabela 2	6,3 mm
Tolerance for cable diameter 2	± 0,2 mm
Struktura kabla	8x0,25 zaslonjeno
Nazivni presek provodnika	0,25 mm ²
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost Bez halogena
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Nickel-plated and gold-plated brass
Material insulation	PP