

Plastično crevo PUN-H-16X2,5-SW-100

Broj artikla: 558255

FESTO

dopušteno u prehrambenom području (postojano na hidrolizu).
Ovaj proizvod nije prikladan za utične priključke CN i PK.



Tehnički podaci

| Svojstvo | Vrednost |
|---|--|
| Spoljašnji prečnik | 16 mm |
| Radius savijanja, merodavan za protok | 88 mm |
| Unutrašnji prečnik | 11 mm |
| Min. radius savijanja | 38 mm |
| Uputstva za korišćenje | TPE-U Ether basiert |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0,095 ... 0,6 MPa |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 6 bar |
| Operating pressure for entire temperature range | -13,775 ... 87 psi |
| Temperature-dependent operating pressure | -0,095 ... 1 MPa |
| Pogonski pritisak zavisn od temperature | -0,95 ... 10 bar |
| Temperature-dependent operating pressure | -13,775 ... 145 psi |
| Napomena za pogonski pritisak | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C |
| Dozvola | TÜV |
| Mesto izdavanja sertifikata | B 013277 0506 00 |
| Pogonski medijum | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| Material fire test | UL94 HB |
| PWIS conformity | VDMA24364-B2-L |
| RSBP classification to CD-0033 | F1a |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe | See Supplementary material information |
| Temperatura okoline | -35 ... 60 °C |
| Težina proizvoda prema dužini | 0,123 kg/m |
| Pneumatski priključak | For push-in connector outside diameter 16 mm |
| Boja | crno |
| Tvrdoća po Shoreu | D 52 +/-3 |
| Materijal - napomena | RoHS komformnost |
| Material tubing | TPE-U(PU) |