



# 連接電纜

## KMP4-25P-5-PVC

料號: 193016

FESTO



### 技術參數

| 特性   | 值                                    |
|--|--------------------------------------|
| 基於標準   | DIN 41652                            |
| Cable identification                                 | 具配件                                  |
| 連接頻率   | 50                                   |
| 產品重量   | 854 g                                |
| Electrical connection 1, function                    | Field device side                    |
| Electrical connection 1, design                      | 有角的                                  |
| Electrical connection 1, connection type             | 插頭插座                                 |
| Electrical connection 1, cable outlet                | Angled                               |
| Electrical connection 1, connection technology       | Sub-D                                |
| Electrical connection 1, number of pins/wires        | 25                                   |
| Electrical connection 1, occupied pins/wires         | 25                                   |
| Electrical connection 1, type of mounting            | 2x M3 screws                         |
| Electrical connection 2, function                    | Controller side                      |
| Electrical connection 2, connection type             | 電纜                                   |
| Electrical connection 2, connection technology       | 開放式終端                                |
| Electrical connection 2, number of pins/wires        | 25                                   |
| Electrical connection 2, occupied pins/wires         | 25                                   |
| 工作電壓範圍 DC  | 0 ... 30 V                           |
| 額定工作電壓 DC  | 24 V                                 |
| 在40°C時的可接受電流負載                                       | 3 A                                  |
| 浪湧強度   | 1 kV                                 |
| 電纜長度   | 5 m                                  |
| 電纜屬性   | Suitable for energy chains           |
| 電纜的測試條件  | 視需求的測試條件                             |
| Bending radius, fixed cable installation             | >= 33 mm                             |
| Bending radius, flexible cable installation          | >= 55 mm                             |
| 電纜直徑   | 10.4 mm                              |
| 電纜直徑公差   | ± 0,5 mm                             |
| 電纜結構   | 25x0,25                              |
| 導體的額定截面  | 0.25 mm <sup>2</sup>                 |
| 導線末端   | Cut off bluntly                      |
| 防護等級   | IP65                                 |
| Note on degree of protection                         | 裝配狀態                                 |
| 環境溫度   | -40 ... 70 °C                        |
| Ambient temperature with flexible cable installation | -5 ... 70 °C                         |
| 儲藏溫度   | -25 ... 75 °C                        |
| CE 符號 (參見符合的標準)                                      | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity)         | To UK RoHS instructions              |
| PWIS conformity                                      | VDMA24364-B2-L                       |
| 材料備註   | 符合 RoHS                              |
| 污染程度   | 3                                    |
| Material cable sheath                                | PVC                                  |
| 電纜外套顏色   | 灰色                                   |
| Material housing                                     | PA                                   |
| 外殼顏色   | 黑色                                   |
| Material seals                                       | NBR                                  |
| Material electrical contact                          | Gold-plated copper alloy             |