


# 馬達電纜

## NEBM-M23G15-EH- -Q7N-R3LEG14

料號: 5251373

FESTO



代表範例

### 技術參數

特性	值
基於標準	EN 61984
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M23x1
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Plugs and cables
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	RJ45 and open end
Electrical connection 2, number of pins/wires	14
Electrical connection 2, occupied pins/wires	12
工作電壓範圍 DC	0 ... 850 V
工作電壓範圍 AC	0 ... 630 V
在40°C時的可接受電流負載	11.7 A
浪湧強度	6 kV
電纜長度	0.5 ... 100 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 48 mm
Bending radius, flexible cable installation	>= 90 mm
電纜直徑	12 mm
電纜直徑公差	± 0,3 mm
電纜結構	4 x 0.75 mm <sup>2</sup> + 1 x (2 x 0.75 mm <sup>2</sup> ) + 1 x (2 x 0.24 mm <sup>2</sup> ) + 2 x 2 x 0.15 mm <sup>2</sup> 已屏蔽
導體的額定截面	0.15 mm <sup>2</sup> 0.24 mm <sup>2</sup> 0.75 mm <sup>2</sup>
導線末端	導線末端套圈
防護等級	IP67
Note on degree of protection	裝配狀態
環境溫度	-40 ... 90 °C
Ambient temperature with flexible cable installation	-25 ... 80 °C
CE 符號 (參見符合的標準)	根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS 不含鹵素
污染程度	1
耐腐蝕等級 CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色
Material insulation	PP